



A turbulent flow, Pressure Compensating dripper available in 3 flows.

### Features

- Take-Apart for easy inspection and cleaning.
- Self-flushing action with insect baffle to minimize blockages.
- PC barbed dripper range: 1/2 gph, 1 gph & 2 gph with 0.16" spout.
- Also available with 0.12" & 0.16" barb outlets.
- Colored bases to identify flow rates.
- 1 gph PC Spike and In-Line Spike models to anchor CETA® at the plant.

### Applications

Pots, planter boxes, balcony patio and landscape applications.



CETA® PC  
1 gph Spike  
with 0.16" Inlet

CETA® PC  
1 gph Spike with  
0.16" In-Line Inlet

Performance	DISCHARGE (gph)		
	1/2 gph	1 gph	2 gph
5	0.41	0.76	1.47
10	0.51	0.92	1.80
15	0.54	1.00	2.08
20	0.57	1.07	2.08
25	0.59	1.12	2.11

\* C<sub>v</sub> for all CETA® PC emitters conforms to ISO 9261

### CETA® PC 1 gph Spike

BASE TYPE	PART NUMBER	PACK QUANTITY	PACKS PER CARTON	CARTON (lbs)
Spike	30625	25	40	13.4
In-Line Spike	30655	25	40	14.4

### CETA® PC with 0.12" Barb Outlet

NOMINAL FLOW	BASE COLOR	PART NUMBER	PACK QUANTITY	PACKS PER CARTON	CARTON (lbs)
1/2 gph	Red	30515	100	50	24.3
1 gph	Black	30525	100	50	24.3
2 gph	Green	30535	100	50	24.3

### CETA® PC with 0.16" Barb Outlet

NOMINAL FLOW	BASE COLOR	PART NUMBER	PACK QUANTITY	PACKS PER CARTON	CARTON (lbs)
1/2 gph	Red	30545	100	50	24.3
1 gph	Black	30555	100	50	24.3
2 gph	Green	30565	100	50	24.3



CETA®  
PC 1/2 gph  
Barb 0.16"  
0.12" or 0.16"  
Outlet

CETA®  
PC 1 gph  
Barb 0.16"  
0.12" or 0.16"  
Outlet

CETA®  
PC 2 gph  
Barb 0.16"  
0.12" or 0.16"  
Outlet

### Specifications

DIMENSIONS		CETA® PC With 0.12" 0.16" Barb Outlet	CETA® PC Spike/In-Line Spike
HEIGHT		1.4"	5.3"
WIDTH		0.8"	1.7"/1.4"
DEPTH		0.6"	0.6"
WEIGHT (approx)		0.07 oz	0.18 oz
UV STABILIZED MATERIALS	BASE/SPIKE CAP DIAPHRAGM ADAPTER	polypropylene polypropylene silicone acetal	polypropylene polypropylene silicone
CONNECTION TYPE: Inlet Outlet		BARB 0.16" BARB 0.12" or 0.16"	BARB 0.16" SPOUT 0.16"